

Material Statement

Dear Customers,

Thank you very much for choosing KUDOS ultrasonic cleaners. To ensure a longer service life of the unit, we would like to ask you to take notice of the fact that the tank of KUDOS ultrasonic cleaners is made of type **SUS304** stainless steel, this type of stainless steel does not resist to acids or alkalines. Only type 316L stainless steel can resist corrosions from acids or alkalines.

For the above reason, please do not use any acids or alkalines as detergents to the ultrasonic cleaner, even of weak acids or alkalines. Acids or alkalines will lead to corrosion to the ultrasonic tank, and result in damages to the circuit board and other parts inside. **Please Only use neutral detergents to the ultrasonic cleaner!**

When using caustic detergents are quite necessary, firstly pour the caustic detergents into a glass container like a beaker, then put the beaker into the ultrasonic cleaner filled with clean water. In this way, corrosion to the ultrasonic tank can be avoided.

Reminder: Leakage result from improper use of caustic detergents is not within the warranty!!!

Thank you.